










































 <p>FIELD INSTRUMENT 6000 ASSEMBLY MN: 213940 PN: FI6000</p>	 <p>HPT FLOW MODULE, FI BASED 120VAC MN: 214091 PN: K6300</p>	 <p>1.75 HPT PROBE MN: 226553 PN: K6052</p>	 <p>2.25 HPT PROBE ASM MN: 214097 PN: K8050</p>	 <p>150-ft. MN: 214095 200-ft. MN: 214096</p> <p>HPT TRUNKLINE SEAL, ORANGE MN: 207772 PN: 37031</p>	
 <p>TRUNKLINE SEAL SPACERS (1 PAIR) MN: 207596 PN: 36378</p>	 <p>HPT SERVICE KIT MN: 205599 PN: 29028</p>	 <p>HPT SCREEN ASM MN: 205558 PN: 28895</p>	 <p>HPT SPRING WASHER (PKG 10) MN: 215453 PN: 52399</p>	 <p>HPT Sensor MN: 210091 PN: 43327</p>	 <p>Coupling HPT TL to HPT Sensor MN: 107963 PN: 48842</p>
 <p>BAND CLAMP No. 7, (PK 10) MN: 220976</p>	 <p>MIP MEMBRANE RATCHET WRENCH ASM. MN: 212094 PN: 48877</p>	 <p>MIP MEMBRANE RATCHET WRENCH HEAD ASM. MN: 212095 PN: 48878</p>	 <p>HPT REF CYL, 1.75 IN. PROBE MN: 212689 PN: 50344</p>	 <p>HPT REF CYL, 2.25 IN. PROBE MN: 211762 PN: 48074</p>	 <p>SC Probe Test Jig MN: 214237 PN: SC563</p>
 <p>EC TEST LOAD, 3 POS MN: 208075 PN: 37785</p>	 <p>HPT CONTROLLER TEST LOAD MN: 206552 PN: 32441</p>	 <p>140 micron filter replacement HPT MN: 110223</p>	 <p>HPT TRUNKLINE-EC PIGTAIL MN: 220974</p>	 <p>HPT TRUNKLINE-SENSOR PIGTAIL MN: 220975</p>	 <p>TERM BLOCK 4 POS GREEN MN: 101465 PN: 7700</p>
 <p>HPT Line Pressure Sensor MN: 112735</p>	 <p>HPT Flow Sensor MN: 106479 PN: 47060</p>				






1.75 HPT Probe

MN: 226553



NEW  HPT GROUND WATER SAMPLER, 2.25 MN: 216100 PN: KS8050	NEW  2.25 in. Water Seal Drive Head (2.25 in. OD) MN: 212089 PN: 48866	 2.25 Connection Tube Hex MN: 219492	 HPT SCREEN ASM MN: 205558 PN: 28895	 HPT SPRING WASHER (PKG 10) MN: 215453 PN: 52399	 BAND CLAMP No. 7, (PK 10) MN: 220976
 HPT Sensor MN: 210091 PN: 43327	 Coupling HPT TL to HPT Sensor MN: 107963 PN: 48842	 BAND CLAMP No. 7, (PK 10) MN: 220976	 HPT TRUNKLINE 150 ft. MN: 214095 PN: K6415	 HPT TRUNKLINE 200 ft. MN: 214096 PN: K6420	NEW  Peristaltic GWS Hex Water Seal MN: 218212
 Hex Water Seal Grouting Spacer MN: 219279	 MBP MECHANICAL BLADDER PUMP MN: 214098 PN: MB470	 MECHANICAL SYRINGE PUMP MN: 234560	NEW  BARB NOSE INTAKE MBP MN: 213376 PN: 51811	 Tube PE 1/4 in. OD x 3/16 in. ID MN: 601062 PN: TB17L	 Tube FEP 1/4 in. OD x 3/16 in. ID x 100 ft. MN: 214252 PN: TB171T



 <p>GWP 1.75 PROBE MN: 230905</p>	 <p>1.75 in. Connection Tube MN: 219594</p>	 <p>Drive Head 1.5 Pin to 1.75 RHSL Box MN: 220545</p>	 <p>1.75 in. Connection Tube with Friction Reducer (2.13 in. O.D.) MN: 225827</p>	 <p>DRIVE HEAD 1.75 RHML PIN X 1.75 RHSL BOX MN: 220130</p>	 <p>BAND CLAMP No. 7, (PK 10) MN: 220976</p>
 <p>GWP HPT SENSOR CABLE MN: 230985</p>	 <p>O-RING FOR 1.75 in. PROBE ROD (PKG 25) MN: 220387</p>	 <p>MBP MECHANICAL BLADDER PUMP MN: 214098 PN: MB470</p>	 <p>BARB NOSE INTAKE MBP MN: 213376 PN: 51811</p>	 <p>MBP SERVICE PARTS KIT MN: 214112 PN: MB7500</p>	 <p>MBP ELECTRIC ACTUATOR MN: 214106 PN: MB6120</p>
 <p>1.75 ADAPTER WELDMENT MBP ACTUATOR MN: 230360</p>	 <p>MBP SS PISTON MN: 230993</p>	 <p>MBP PISTON O-RING 10/PKG MN: 230914</p>	 <p>MBP PISTON CUP SEAL 10/PKG MN: 230915</p>	 <p>HPT SPRING WASHER (PKG 10) MN: 215453 PN: 52399</p>	 <p>HPT SCREEN ASM MN: 205558 PN: 28895</p>
 <p>Tube PE 1/4 in. OD x 3/16 in. ID MN: 601062 PN: TB17L</p>	 <p>Tube FEP 1/4 in. OD x 3/16 in. ID x 100 ft. MN: 214252 PN: TB171T</p>				



GWP 1.75 Probe

MN: 230905